



GENERAL DESCRIPTION

5-ply Foldable Protective Mask

- ❖ 95% filter efficiency of 0.3 micron particles
- ❖ Inspiratory Resistance < 350 Pa
- ❖ Expiratory Resistance < 250 Pa
- ❖ Adjustable and metal nose clip
- ❖ 3D foldable design
- ❖ Elastic ear-loop, soft fabric
- ❖ Non-sterile, non-medical
- ❖ Size - One Size Fits Most

MATERIAL COMPOSITION

- ❖ Outer Layer - Spunbonded Polypropylene 60gsm \pm 2gsm
- ❖ 2-ply Filter Layer - Melt-blown filter paper 25gsm \pm 2gsm
- ❖ 2-ply Inner Layer - Spunbonded polypropylene 25gsm \pm 2gsm
- ❖ Ear Loop - Elastic spandex, latex free, flat ear-loop
- ❖ Nose Strip - Double Wire with Plastic Coating



DIMENSION

- ❖ Size - 15.5X11cm \pm 0.3cm
- ❖ Ear Loop - 21.0cm \pm 0.3cm
- ❖ Nose Strip - 9.0cm \pm 0.5cm
- ❖ Packing - 10pcs/bag, 1200pcs/carton, or as requested
- ❖ Inner Bag - OPP Bag (17x24cm)
- ❖ Outer Case - 5ply Corrugated Paperboard (29x33x45cm)

INTENDED USAGE

- ❖ Civil Grade, Non-Medical use
- ❖ The mask is used for protection against particles, such as those from minerals, coal, iron, ore, flour, and certain other substances as well as liquid or non-oil-based particles from sprays that do not also emit oil aerosols or vapors.

DO NOT USE FOR

- ❖ The mask is not for gases, vapors, and oil aerosols.
- ❖ The mask is not for particulate concentrations exceeding 10X PEL/OEL.
- ❖ The mask is not guaranteed to protect against the risk of contracting a disease or infection.

TIME USE LIMITATION

- ❖ Shelf Life: 3 years.
- ❖ Replace the mask when it becomes dirty, damaged, or difficult to breathe through.
- ❖ Storage and transport: keep in a ventilated and dry room, prevent heavyweight, direct sunlight, rain, and snow immersion.

For More Information:

86.512.6262.1607
sales@wellmien.com
www.wellmien.com

Wellmien