



## GENERAL DESCRIPTION

### Isolation Gown, ASTM Level 3

- ❖ Water Resistance:Hydrostatic Pressure Test  
Main Body Fabric(CM H2O) > 50  
Sleeve(CM H2O) >50  
Belt(CM H2O) >50
- ❖ Test Standard: AATCC127-2018
- ❖ Water Resistance:Impact Penetration Test  
Main Body Fabric(gram) < 1g  
Sleeve(gram) < 1g  
Belt(gram) < 1g
- ❖ Test Standard: AATCC42-2017

## DIMENSION

- ❖ Material: Polypropylene
- ❖ Size: S --- 2XL
- ❖ Grammage: 36gsm -- 90gsm
- ❖ Color: White, Yellow, Blue
- ❖ Process: Ultrasonic , knit cuff , velcro hook and loop , spot welding waist tie
- ❖ Package: 10pcs/bg 10bg/cs
- ❖ Carton Size: 68.6X33X30 CM



## Application

- ❖ Used in MODERATE risk situations.
- ❖ Provides a barrier to larger amounts of fluid penetration through splatter and more fluid exposure through soaking than Level 2.
- ❖ Arterial blood draw, Inserting an IV, Emergency Room, Trauma

## INTENDED USAGE

- ❖ ASTM L 3 isolation gowns are intended for use by the general public or health care workers to reduce the risk of viral transmission and fluid spillage.

## TIME USE LIMITATION

- ❖ Shelf Life: 3 years.
- ❖ Replace the gown when it becomes dirty, damaged, or difficult to breathe through.
- ❖ Storage and transport: keep in a ventilated and dry room, prevent heavyweight, direct sunlight, rain, and snow immersion.

For More Information:

86.512.6262.1607  
sales@wellmien.com  
www.wellmien.com

 **Wellmien**